

Апматы (7273)495-231
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-61

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(7172)727-132

Киргизия +996(312)96-26-47

<https://mikrotest.nt-rt.ru/> || mei@nt-rt.ru

Plant Growing Booth



Plant Growing Booth; It has been developed to simulate real climatic conditions by controlling temperature, humidity and day-night light cycles. Perfect design of the device, MBB Series; It is used in studies such as plant growth, seed shaping, acclimatization of plants to new climatic conditions, production of cell and tissue culture, genetic research of plants, cell and protoplasm breeding, incubation and growth of insects.

Considering the extreme cold and hot temperatures, insulation is of great importance for the efficiency of the product. Left and right windows consisting of double glazing provide excellent thermal insulation. The rear surface of the cell and the door are insulated with polyurethane. The double door gasket ensures tightness even under the most extreme climatic test conditions.

The cell of the MBB Series is illuminated from two surfaces, on the right and on the left. In this way, the movement of sunlight can be animated. The illumination on both surfaces can be programmed separately according to the 24-hour period.

TECHNICAL SPECIFICATIONS

Model	MBB-250	MBB-400	MBB-600
Kullanılabilir Hacim	250 Lt.	400 Lt.	600 Lt.
Nemsiz Sıcaklık Aralığı	Aydınlatmasız -10°C / +60°C - Aydınlatmalı 10°C / +60°C		
Nemli Sıcaklık Aralığı	10°C / + 60°C		
Sıcaklık Ayar ve Okuma Hassasiyeti	0,1°C		
Azami Işık Şiddeti	10.000 Lux		
Aydınlatma Zamanlayıcısı	0-999 Saat 59 dk. Ve Süresiz		
Program Basamak Sayısı	10		
Program Tekrar Sayısı	999		
Raf Sayısı	3/7	4/10	4/12
İç Yüzey Yapısı	Paslanmaz Çelik		
Dış Yüzey Yapısı	Epoksi Boyalı, Galvaniz Çelik		
İç Ölçüler (E x D x Y) (cm)	55x55x85	65x65x95	75x70x110
Dış Ölçüler (E x D x Y) (cm)	75x75x175	85x85x180	95x90x195
Kuruluş Güç	6000 V		
Güç Değerleri	220V 50Hz		